

CRL 103 Power Unit Mainframe

CRL 104 Power Unit Channel

Multi-Channel Five-Lite System

The CRL 103 Power Unit Mainframe and CRL 104 Power Unit Channels power the Multi-Channel Five-Lite System. The CRL 103 Power Unit Mainframe can hold up to six CRL 104 Power Unit Channels. The CRL 103 Power Unit Mainframe also has an output to power Theta phones and a 6 volt output to power auxiliary devices such as a RSS 605 Power Unit to operate a hygiene status system. 12 volt output to the orange terminal screws is electronically limited to 8 amperes by the CRL 103 Power Unit Mainframe. The CRL 104 Power Unit Channels electronically limit their 6 volt output to 12 amperes.



CRL 103 Power Unit Mainframe will be in reset mode for the first 5 seconds after being plugged in and will be in reset mode for 5 seconds after an overload on the orange terminal screws. While in reset mode the trouble indicator light will flash as buttons are pressed to light lights. The trouble will not light during normal operation if the system.

CRL 103 Power Unit Mainframe has a 3AG 4 ampere fuse next to the power cord. A 3AG 5 ampere fuse next to the 6 volt output protects the 6 volt output.